





MICE Steps




STEP I

done
2011: EMR




STEP II

skip




STEP III/III.1

skip




STEP IV

Spring 2012 →



STEP V



STEP VI




ϵ_{in}

ϵ_{out}

STEP IV.0

Vacuum


- Diffuser
- Spectrometers
- Trackers
- EMR
- Focus coil



STEP IV.1

Solid absorbers


- Plastic 50 mm
- LiH 65 mm
- Be 34 mm
- Al 23 mm
- Fe 9 mm
- Cu 8 mm
- Wedge



STEP IV.2

Liquid absorbers

- LiqH2 350 mm
- LiqHe?



PREMIUM ON FAST and ROBUST PUSH-PULL OPERATION OF FC MODULE