## **Session Program**

25-29 Jun 2018



## **MEDSI 2018**

## **CORE TECHNOLOGY DEVELOPMENTS**

Venue CITÉ INTERNATIONALE UNIVERSITAIRE 17 Boulevard Jourdan 75014 Paris

## Wednesday 27 June

14:10-1	WEOPMA07: Development of a New Sub-4k ARPES Endstation at F
<b>Speaker</b> Daniel Tru	tmann
14:30-1 WEOPM in vacu	a:50 A02: Non-contact luminescence lifetime cryothermometry for applicati um environment
Speaker Vitaliy My	khaylyk
CORE - Session	<b>TECHNOLOGY DEVELOPMENTS</b> Location: Venue, CITÉ INTERNATIONALE UNIVERSITAIRE 17 Boulevard Jourdan 75014 Paris
WEODN	
Sample Speaker Xinyu Wa	A03: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL
Sample Speaker Xinyu Wa 15:40-1 WEOPM Compac	A03: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL <sup>ng</sup> 5:00 A04: Mechanical Design of a New Precision Alignment Apparatus for ct X-ray Compound Refractive Lens Manipulator
Sample Speaker Xinyu Wa 15:40-1 WEOPM Compace Speaker Deming S	A03: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL <sup>ng</sup> 5:00 A04: Mechanical Design of a New Precision Alignment Apparatus for at X-ray Compound Refractive Lens Manipulator
Sample Speaker Xinyu Wa 15:40-1 WEOPM Compace Speaker Deming S 16:00-1 WEOPM Method	A03: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL <sup>ng</sup> A04: Mechanical Design of a New Precision Alignment Apparatus for at X-ray Compound Refractive Lens Manipulator <sup>hu</sup> A05: Application of Industry Recognised Development Tools and ologies, such as Design for Six Sigma to Facilitate the Efficient Deliver
Sample Speaker Xinyu Wa 15:40-1 WEOPM Compace Speaker Deming S 16:00-1 WEOPM Method Innovat	AU3: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL <sup>ng</sup> A04: Mechanical Design of a New Precision Alignment Apparatus for at X-ray Compound Refractive Lens Manipulator hu A05: Application of Industry Recognised Development Tools and ologies, such as Design for Six Sigma to Facilitate the Efficient Deliver ive and Robust Engineering Solutions in Synchrotron
WEOPM Sample Speaker Xinyu Wa 15:40-1 WEOPM Compace Speaker Deming S 16:00-1 WEOPM Method Innovat Speaker Sarah An	AU3: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL ng A04: Mechanical Design of a New Precision Alignment Apparatus for at X-ray Compound Refractive Lens Manipulator hu S20 A05: Application of Industry Recognised Development Tools and ologies, such as Design for Six Sigma to Facilitate the Efficient Delivery ive and Robust Engineering Solutions in Synchrotron
WEOPM Sample Speaker Xinyu Wa 15:40-1 WEOPM Compace Speaker Deming S 16:00-1 WEOPM Method Innovat Speaker Sarah An	AU3: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL ng A04: Mechanical Design of a New Precision Alignment Apparatus for at X-ray Compound Refractive Lens Manipulator hu A05: Application of Industry Recognised Development Tools and ologies, such as Design for Six Sigma to Facilitate the Efficient Delivery ive and Robust Engineering Solutions in Synchrotron
Sample Sample Speaker Xinyu Wa 15:40-1 WEOPM Compace Speaker Deming S 16:00-1 WEOPM Method Innovat Speaker Sarah An 16:20-1 WEOPM two full	AU3: Application of Additive Manufacturing in the Development of a Holder for a Fixed Target Vector Scanning Diffractometer at SwissFEL ng A04: Mechanical Design of a New Precision Alignment Apparatus for at X-ray Compound Refractive Lens Manipulator hu 3:20 A05: Application of Industry Recognised Development Tools and ologies, such as Design for Six Sigma to Facilitate the Efficient Delivery ive and Robust Engineering Solutions in Synchrotron Macdonell 3:40 A06: A compact and calibratable von Hamos X-Ray Spectrometer based -cylinder HAPG mosaic crystals for high-resolution XES